



SKU # H4D-3-10K-SLIM

Part # 1002048

Description

H4-3 HID Digital Super-Slim Ballast Kit

Categories HID & LED Headlights, HID Headlight Conversions

Sub-Categories HID Conversion Kits, D-Elite HID Headlight Kit

UPC 811712029322

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

DC Slim HID Kit - 10K

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

10,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

Current Draw

Wattage

35-Watts

Chip Type

XENON HID

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

10,000K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern

N/A



Product Information

Economically Priced SLIM DC Technology Kits • 12 Month Warranty • SMT Technology • High quality igniter system • 35W ballast power • SLIM weatherproof design • Kit includes: -(2) 35W Ballasts -(2) 35W HID Bulbs -Hardware - Instruction Card • Bi-xenon kits include high/low control pack harness

Est. Labor

Hours

Gross Weight

1.80

Width

7.50

Net Weight

1.60

Height

10.00

DIM Weight

1.08

Depth

2.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com