SKU # H4-3-3K-G4-CANBUS



Part # 1001833

Description

H4-3 Bi-Xenon GEN4® Canbus HID SLIM Kit

Categories HID & LED Headlights, Powersports, HID Headlight Conversions

Sub-Categories

HID Conversion Kits, GEN4® HID Headlight Kits, Gen4 CANBUS HID Headlight Kit

UPC 817363019613

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition
New

Manufacturer
Race Sport Lighting

EZ Category
Gen4 CANBUS HID Kit - 3K

Harmonization Code
8512.20.2080

Universal
YES

Life Expectancy
10,000 hours

SEMA Product
Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity
Headlight Conversion Kit

Operating Voltage

Current Draw

Wattage
35-Watts

Chip Type
XENON HID

IP Rating
IP67

LUX

Kelvin (ColorTemperature)
3,000K

Universal or Vehicle Specific
Universal

Made In
China

Warranty
3 year

Lumens

Beam Pattern
N/A

Product Information

Solve All Your Problems Race Sport Lighting's Gen4® 35W HID Kits are a solve-all solution to your headlight problems. With built in error light and RF interference prevention circuitry you don't have to worry about dash lights or static on your radio. All of these features are packed into a slim, sturdy design. • 3 Year Warranty • SLIM weatherproof design • Error light prevention circuitry built in • RF interference prevention circuitry built in • High quality igniter system • 35W ballast power • Oriented for CANBUS vehicles model year 2005 and newer • Kit includes: -(2) 35W CANBUS Ballasts -(2) 35W HID Bulbs -Hardware -Instruction Card • Bi-xenon kits include high/low control pack harness

Est. Labor	Hours		
Gross Weight	2.80	**Width**	7.50
Net Weight	2.60	**Height**	4.00
DIM Weight	2.16	**Depth**	10.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov