



SKU # H8-10K-G3-CANBUS

Part # 1002350

Description

H8 GEN3® Canbus HID SLIM Ballast Kit

Categories HID & LED Headlights, HID Headlight Conversions

Sub-Categories HID Conversion Kits, Gen3 CANBUS HID Headlight Kit

UPC 817363016018

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Gen3 CANBUS HID Kit - 10K

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

10,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

Current Draw

Wattage

35-Watts

Chip Type

XENON HID

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

10,000K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

3 year

Lumens

Beam Pattern

N/A



Product Information

All-In-One Super SLIM CANBUS Technology Race Sport Lighting's Gen3® 35W Canbus HID Kits feature internal error light prevention circuitry, stopping those annoying bulb out indicators you get with other kits. • 3 Year Warranty • SLIM weatherproof design • Error light prevention circuitry built in • High quality igniter system • 35W ballast power • Oriented for CANBUS vehicles model year 2005 and newer • Kit includes: -(2) 35W CANBUS Ballasts -(2) 35W HID Bulbs -Hardware -Instruction Card • Bi-xenon kits include high/low control pack harness

Est. Labor

Hours

Gross Weight

2.80

Width

7.50

Net Weight

2.60

Height

4.00

DIM Weight

2.16

Depth

10.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com