



SKU # MS-27W-DP-R

Part # 1003191

Description

27W CREE LED Underwater Drain Plug Light (Red) 1000 Lumens - 316 Marine Grade Stainless Steel



Categories Marine, Marine, Marine Sport Lighting

Sub-Categories

Marine Sport® Heavy Duty Professional LED Underwater Lights, Marine Sport® Stainless Steel Underwater LED Lighting Systems IP68, Underwater LED Lighting

UPC 812867028413

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Marine Sport Lighting

EZ Category

Marine Underwater Drain Plugs

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product

Marine All-Around Light

Part Type ID 57170

Reverse Polarity

Marine All-Around Light

Operating Voltage

Current Draw

Wattage

27-Watts

Chip Type

CREE

IP Rating

IP68

LUX

Product Information

- IP68 waterproof rating
- 12-24V battery or power sources only.
- Standard "1/2 NPT thread type, connected with 2 meters cable.
- Lights are for underwater use only; do not operate it out of water.
- Not only attractive but also functional in aiding the attraction of fish.
- Extremely luminous LED cluster, makes this most powerful led drain plug on the market.
- Connected with waterproof connector in order to easy installation, no drilling hole are needed, just screw it into the existing drain plug holes on your boat.
- 1 Year Warranty (1000 Lumens)

Est. Labor

1 Hours

Gross Weight

0.40

Width

4.50

Net Weight

0.40

Height

4.50

DIM Weight

0.33

Depth

2.25

Kelvin (ColorTemperature)

Red

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

1,000lm

Beam Pattern

Flood

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com