



SKU # RS08RGB

Part # 1006399

Description

ColorADAPT 8-Piece Light 6SMD POD RGB Multi-Color Accent Kit with remote control

Categories

ColorADAPT RGB LED Accent Kits, Motorcycle Lighting, Interior/Exterior Accent LED

Sub-Categories

LED Accent Kits, Flexible Dashboard Strip Lighting

UPC 817999022483

Unit of Measure Kit

Related Skus:

RS3EW, RS12EW

Cross Sell Skus:

RSWWKIT,RSRGB15,RSRGB152R,RSRGB15-C

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

ColorADAPT RGB Product

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product Wheel Accent Light

Part Type ID 15452

Reverse Polarity

Wheel Accent Light

Operating Voltage

12VDC

Current Draw

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

RGB

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern



Product Information

Race Sport Lighting's Pod light kits are pre-designed to give you the RGB multi-color light that you want and to fit anywhere on any vehicle. They can be mounted several different ways including flush, underneath, inside, and in outside locations. Want to mount them as rock lights in the wheel wells? Sure, you can do that too. Each kit comes with a sleek remote fab to control the whole system.

Est. Labor

1 Hours

Gross Weight

0.40

Width

3.50

Net Weight

0.40

Height

9.00

DIM Weight

0.79

Depth

3.50

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov