



SKU # RS180

Part # 1005002

Description

31.5in ECO-LIGHT LED Light Bars w/ 3D Reflector Optics & CREE LED



Product Information

Race Sport Lighting's ECO-Light series LED light bars feature proprietary optics for unmatched light output, all at an economical price point making them our premier entry level LED bar. • 180W • 14.2 AMPs • 10,700 Lumens • Combination light pattern • 9-16v Voltage Range • Bar Height: 3" (75.75mm) • Mounted Height (Level to Mounting Surface): 4" (101.875mm) • 32" Bar Length End-to-End • 35" Bar Length including Mount • 1 Year Warranty

Categories Truck, Powersports, Truck, LED Light Bars

Sub-Categories

LED Light Bars, Straight ECO-LIGHT LED Light Bars with 3D Reflector Opticals, LED Light Bars, Eco Series Dual Row Light Bars

UPC 814843021821

Unit of Measure EA

Related Skus:

RSTP016, RS-HARN-SS2

Cross Sell Skus:

RS3X3ECO,RS3X3FECO

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

ECO Series Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Light Bar

Part Type ID 1069

Reverse Polarity

Light Bar

Operating Voltage

9-16VDC

Current Draw

14.2A

Wattage

180-Watts

Chip Type

PHILLIPS

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

10,700lm

Beam Pattern

Combo

Est. Labor

1 Hours

Gross Weight

10.60

Width

5.00

Net Weight

10.60

Height

6.50

DIM Weight

7.95

Depth

34.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com