



SKU # RS36

Part # 1004971

Description

6.5in ECO-LIGHT LED Light Bars w/ 3D Reflector Optics & CREE LED



Categories Truck, Powersports, Truck, LED Light Bars

Sub-Categories

LED Light Bars, Straight ECO-LIGHT LED Light Bars with 3D Reflector Opticals, LED Light Bars, Eco Series Dual Row Light Bars

UPC 814843021791

Unit of Measure EA

Related Skus:

RSTP016, RS-HARN-SS2

Cross Sell Skus:

RS3X3ECO,RS3X3FECO

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

ECO Series Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Light Bar

Part Type ID 1069

Reverse Polarity

Light Bar

Operating Voltage

9-16VDC

Current Draw

2.8A

Wattage

36-Watts

Chip Type

PHILLIPS

IP Rating

IP67

LUX

Product Information

Race Sport Lighting's ECO-Light series LED light bars feature proprietary optics for unmatched light output, all at an economical price point making them our premier entry level LED bar. No job is too big or small for these high power light bars to clear the path. This Nationwide top selling light bar is exactly what you need for every job. • 36W • 2.8 AMPs • 2,340 Lumens • Combination light pattern • 9-16v Voltage Range • Bar Height: 3" (75.75mm) • Mounted Height (Level to Mounting Surface): 4" (101.875mm) • 8" Bar Length End-to-End • 11" Bar Length including Mount • 1 Year Warranty

Est. Labor

1 Hours

Gross Weight

3.25

Width

5.25

Net Weight

2.75

Height

6.50

DIM Weight

2.46

Depth

10.00

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

2,340lm

Beam Pattern

Combo

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com