



SKU # RS3X3FECO

Part # 1006981

Description

NEW - ECO-LIGHT LED High Power FLUSH MOUNT Style Auxiliary Lights (Sold as Pairs)

Categories LED Spots and Auxiliary Lighting, LED Light Bars, LED Light Bars

Sub-Categories

Street Series Spot Lights & Accessories, Eco Series Dual Row Light Bars, ECO-SLIM Single Row Light Bars

UPC 817999026207

Unit of Measure PR

Related Skus:

RSLEDH2, RS-SS-HARN

Cross Sell Skus:

RS3X3ECO,RS36,RS120

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

ECO Series Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product Off-Road Light

Part Type ID 15431

Reverse Polarity

Off-Road Light

Operating Voltage

9-16VDC

Current Draw

4A

Wattage

Chip Type

PHILLIPS

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

5,900 Lm

Beam Pattern

Spot



Product Information

These amazing pair of ECO-SERIES LED Flush Mount lights will give users the brightness and durability in auxiliary lights they are looking for. These super high power auxiliary work lights are the perfect solution for your work light needs. Unlike most flush mounts on the market that only give you spot or flood, these revolutionary cubes give off two types of beam patterns that give you maximum light spread to complete the job. Great for mounting in bumpers, work racks, etc. . LED Power: 48W . Dimensions: 3.0 inch . Operating Voltage: 10-30V DC . 16pcs*3w high intensity 3030 LEDs . Optional Color: Black, White . Color Temperature: 6000K . Material: Diecast aluminum housing . Lens material: PMMA . COMBO Beam: Pencil + spot . 30,000 hours above life time . Waterproof rate: IP 67

Est. Labor

1 Hours

Gross Weight

2.00

Width

5.25

Net Weight

2.00

Height

4.00

DIM Weight

1.21

Depth

8.00