



SKU # RS5M5050IP67-C

Part # 1006964

Description

NEW - 16.4ft 5-Meter 5050 RGB Chasing Function Strip Lighting and Controller - IP67 Rated with EPOXY protection



Categories LED Tape Strip Lighting

Sub-Categories 5050 Professional Tape Strip Reels

UPC 817999026320

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Chasing Strip Lights

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

Product Information

NEW - 16.4ft 5-Meter 5050 RGB Chasing Function Strip Lighting and Controller - IP67 Rated with EPOXY protection

Est. Labor

Hours

Gross Weight

2.20

Width

7.50

Net Weight

2.20

Height

2.00

DIM Weight

1.08

Depth

10.00

SEMA Product Interior Accent Light

Part Type ID 18826

Reverse Polarity

Interior Accent Light

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

RGB

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern

Linear

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com