



SKU # RS5M5050ISB

Part # 1004899

Description

16.4 feet (5M) 5050 Non-waterproof LED Tape strip lighting reel with no epoxy in Blue Color



Categories Golf Cart Lighting, Auto Interior & Exterior, LED Tape Strip Lighting

Sub-Categories

Interior Accent Lighting, LED Tape & POD strips, Non-Epoxy Tape Strips

UPC 817999020052

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

Product Information

16.4 feet (5M) 5050 Non-waterproof LED Tape strip lighting reel with no epoxy in Blue Color

Est. Labor

Hours

Gross Weight

0.10

Width

6.00

Net Weight

0.10

Height

7.25

DIM Weight

0.08

Depth

0.25

SEMA Product Interior Accent Light

Part Type ID 18826

Reverse Polarity

Interior Accent Light

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

IP65

LUX

Kelvin (ColorTemperature)

Blue

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern

Linear

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com