



SKU # RS5MVS67RGB

Part # 1007321

Description

NEW - V-Sport Plasma 16.4ft IP67 LED Solid Tape Strip Reels with Heavy Duty 3M Adhesive - RGB MULTICOLOR with Remote and Retail Box



Categories LED TAPE STRIP LIGHTING, Auto Interior & Exterior

Sub-Categories V-Sport Plasma Solid Strips, LED Accent Bars

UPC 810077230480

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

V-Sport Tape Strip Lighting

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Interior Accent Light

Part Type ID 18826

Reverse Polarity

Interior Accent Light

Operating Voltage

12VDC

Current Draw

0.5-2.0A

Wattage

14-Watts

Chip Type

IP Rating

IP67

LUX

Product Information

Designed by popular demand for a smooth and steady flow of accent lighting in your projects. Available in either IP65 or IP67, these durable yet flexible V-Sport solid custom tape strips do the job! No more placing expensive clouded acrylic in front of strips to make them appear solid and not separated. This strip does it all for you. Voltage : DC12V Work power : 14W±1W per Meter Lumen: 90±10 Per Watt LED Quantity:336pcs/M

Est. Labor

Hours

Gross Weight

0.10

Width

8.00

Net Weight

0.10

Height

9.25

DIM Weight

0.13

Depth

0.25

Kelvin (ColorTemperature)

RGB

Universal or Vehicle Specific

Universal

Made In

CN

Warranty

1 year

Lumens

90lm

Beam Pattern

Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com