



SKU # RS6L18WPR

Part # 1004912

Description

Street Series 18W 6-LED Bottom Mount LED Spot Lights (Pair)

Categories Agricultural, Powersports, Truck

Sub-Categories

STREET Series LED Spot Lights, STREET Series LED Spot Lights, Auxiliary Spot & Floods

UPC 814843028387

Unit of Measure PR

Related Skus:

RS-27W-S-2, RS-27W-R-2

Cross Sell Skus:

RSTP016

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Street Series Aux Spots

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Off-Road Light

Part Type ID 15431

Reverse Polarity

Off-Road Light

Operating Voltage

9-32VDC

Current Draw

3.0 Amps

Wattage

18-Watts

Chip Type

EPISTAR

IP Rating

IP67

LUX

3,000LUX

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

3 year

Lumens

3,000lm

Beam Pattern

Spot



Product Information

At 2.5", these 6-LED 18W spots are some of our lowest profile Street Series spot lights. Their small size makes them perfect for mounting to the bottom of a bumper, a bull bar, or anywhere else you can think of, as fog lights, auxiliary lighting, reverse lights, or work lights. Kit Contents • (2) 6-LED 18W Bottom Mount Spots • (2) Mounting Brackets • Hardware & Instructions Specifications • 18W Per Spot (36 Watts Total for Kit) • 1.5 Amps per light (3 Amp Total for Kit) • Operating Voltage: 9-32V DC • Working Temperature: -40~85 degree • Material: Die-cast aluminum housing • Mounting Bracket: Stainless steel • Beam angle: 30° • Mounting stud is 1" long (30mm). Thread size is 5/16" (8mm) • 3 Year Warranty -3,000 LUX Total Light Output

Est. Labor

1 Hours

Gross Weight

2.15

Width

4.50

Net Weight

2.15

Height

4.00

DIM Weight

0.91

Depth

7.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com