



SKU # RS72

Part # 1004987

Description

12.5in ECO-LIGHT LED Light Bars w/ 3D Reflector Optics & CREE LED



Categories Truck, Powersports, Truck, LED Light Bars

Sub-Categories

LED Light Bars, Straight ECO-LIGHT LED Light Bars with 3D Reflector Opticals, LED Light Bars, Eco Series Dual Row Light Bars

UPC 814843021807

Unit of Measure EA

Related Skus:

RSTP016, RS-HARN-SS2

Cross Sell Skus:

RS3X3ECO,RS3X3FECO

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

ECO Series Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Light Bar

Part Type ID 1069

Reverse Polarity

Light Bar

Operating Voltage

9-16VDC

Current Draw

5.7A

Est. Labor

1 Hours

Gross Weight

4.75

Width

5.25

Net Weight

4.06

Height

6.50

DIM Weight

3.99

Depth

16.25

Wattage

72-Watts

Chip Type

PHILLIPS

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

4,680lm

Beam Pattern

Combo

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com