



SKU # RSBARCON1

Part # 1005120

Description

Remote Control Kit for Light Bar or LED Work Light (Rated for Spots or Smaller Bars)



Categories

Truck, Commercial, Truck, Auto Interior & Exterior, Powersports, Agricultural, Truck, LED Light Bars

Sub-Categories

Mounting Brackets, Harness and Locks for Light Bars, Light Bar Covers, Locks and Harnesses, Harness and Locks for Light Bars, STREET Series Parts & Accessories, STREET Series Parts & Accessories, Light Bar Covers, Locks and Harnesses, Light Bar Accessories

UPC 812867027300

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Light Bar Parts

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

Product Information

LED Light Bar or Spot controller, great for use with work lights • Plug-&-Play DT Connector • IP 67 Dust and water Proof rating • Adds Strobe and Dimming Function • Remote Control Kit for Light bar or LED Work Light • Max Output 240watt 20A @12v, (Great for light bars from 4"-42") • 1 Year Warranty

Est. Labor

Hours

Gross Weight

1.10

Width

6.75

Net Weight

1.10

Height

3.25

DIM Weight

1.89

Depth

12.00

SEMA Product

Strobe Light Control Module Connector

Part Type ID 49176

Reverse Polarity

Strobe Light Control Module Connector

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

N/A

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov