



SKU # RSBO180

Part # 1006590

Description

BLACKED OUT® Series 30in Straight, Double Row, Silver Combo-Flood/Beam Straight Hi Performance Light Bar 180w



Categories Truck, LED Light Bars

Sub-Categories LED Light Bars, Blacked Out Dual Row Bars

UPC 817999023718

Unit of Measure EA

Related Skus:

RSLEDH1, RS0007, RSTP016, RS-HARN-SS2

Cross Sell Skus:

FHDHB1116,FHDHB17UP,DHDHB17UP,GMHB20UP

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Blacked Out Series Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Light Bar

Part Type ID 1069

Reverse Polarity

Light Bar

Operating Voltage

12-24VDC

Current Draw

Wattage

180-Watts

Chip Type

CREE

IP Rating

IP67

LUX

Product Information

Race Sport Lightings Blacked Out® Series LED Light Bars are a trademarked product line that gives you extremely high LUX output and a completely black face for those doing away with the chrome. Looking for a light bar that blends perfectly with your Blacked out look? Then look no further, our Blacked Out® light bars are made extremely durable and have extremely high light output performance

- 50,000 hour life span
- 12-24v voltage range
- Color Temperature: 6500K
- Waterproof Certified: IP67
- Operation Temp: -40°C-80°C
- Durable aluminum casing
- Combo Beam Optics
- 3-Year Warranty

32.25 inch end to end 30.25 lens length 3.25 inch height 3.5 inch depth

Est. Labor

Hours

Gross Weight

10.60

Width

5.25

Net Weight

10.60

Height

6.50

DIM Weight

8.35

Depth

34.00

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

3 year

Lumens

10,700lm

Beam Pattern

Combo

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com