



SKU # RSCAS002

Part # 1006686

Description

Canbus All Solution Decoder for 9005, 9006, 9012, H10, H12 - Plug N Play with LED and HID Kits - Sold in Pairs

Categories

HID & LED Headlights, HID & LED Headlights, LED Headlight Conversions, HID Headlight Conversions

Sub-Categories

HID Interface Solutions, LED Conversion Kits, LED Interface Solutions, HID Interface Solutions

UPC 817999024487

Unit of Measure PR

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

LED Decoders

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

10,000 hours

SEMA Product

Forward Light Harness Connector

Part Type ID 21278

Reverse Polarity

Forward Light Harness Connector

Operating Voltage

Current Draw

Wattage

N/A

Chip Type

N/A

IP Rating

IP67

LUX

N/A

Kelvin (ColorTemperature)

N/A

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

N/A

Beam Pattern

N/A



Product Information

Race Sport Lighting's Official Canbus Decoder Interfaces help LED Conversion kits communicate without errors from the vehicles CPU to the LED system itself. -Plugs in-line with Race Sport Lighting HID and LED Kits to eliminate most CANBUS interface issues -New technology eliminates need for golden heat sink resistors. -Waterproof IP68 -Highly recommended to put on any premium headlight or fog-light upgrades. -Sold as Pair

Est. Labor

Hours

Gross Weight

0.10

Width

3.50

Net Weight

0.10

Height

1.00

DIM Weight

0.22

Depth

8.75