



SKU # RSDSD4V2

Part # 1007368

Description

NEW - D4 8000 Lumen D Series Projector Compliant OEM Canbus LED headlight kit
6000 Kelvin - Sold in Pairs



Categories LED Headlight Conversions

Sub-Categories DRIVE Series V2 CANBUS

UPC 810077230190 Unit of Measure Kit

Related Skus:

Cross Sell Skus:
RSD4LED

Condition New Manufacturer Race Sport Lighting EZ Category V2 Drive Series CANBUS Kits

Harmonization Code 8512.20.2080 Universal Life Expectancy 50,000 hours

SEMA Product Headlight Bulb Part Type ID 11701

Reverse Polarity Headlight Bulb Operating Voltage 12VDC Current Draw

Wattage Chip Type IP Rating LUX
IP65 5,000lx

Product Information

Now replace those D-series OEM bulbs with LED technology that performs to the Max. In the past, HID D-Series bulbs were your only option, but now our D Series LED bulb line up gives you more options for premium replacement performance in your vehicle. Voltage range : DC9-16V Work power : 43W±2W Lumen: 8,000LM per pair LED Quantity:4PCS per pair

Est. Labor	0.6 Hours		
Gross Weight	1.10	Width	7.25
Net Weight	1.10	Height	2.50
DIM Weight	0.95	Depth	7.25

Kelvin (ColorTemperature) 6,000K Universal or Vehicle Specific Universal

Made In CN Warranty 1 year Lumens 9,000lm Beam Pattern Linear

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com