



SKU # RSLJ7W

Part # 1005286

Description

LED Rocker Switch w/ White LED Radiance (Driving Lights)

Categories

Auto Interior & Exterior, Golf Cart Lighting, Powersports, Agricultural, Truck, LED Switches

Sub-Categories

LED Switches, LED Swtiches, Logo Specific LED Rocker Switches, Logo Specific LED Rocker Switches, LED Logo Rocker Switches, LED Illuminated Logo Rocker Switches

UPC 814843027458

Unit of Measure EA

Related Skus:

RS5PPWSS, RS2PRS, RS3PRS, RS4PRS, RS6PRS, RS5PRS

Cross Sell Skus:

RSBLHB3W-1,RSBLHB3W

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

LED Rocker Switches

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product

Rocker Switch and Cover Set

Part Type ID 20511

Reverse Polarity

Rocker Switch and Cover Set

Operating Voltage

Current Draw

Est. Labor

0.3 Hours

Gross Weight

0.10

Width

3.25

Net Weight

0.10

Height

3.75

DIM Weight

0.09

Depth

1.00

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

White

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern



Product Information

Race Sport Lighting's single-pole, single-throw (SPST) LED Rocker Switches let you quickly control your lights on your off-road vehicle, truck, ATV, UTV, or boat. The switch also features two independently powered LED indicators, and easily installs in industry standard panel cutouts with the included rubber gasket. • Amps: 20A • Input Voltage: DC12V • CE/RoHS Compliant • (5) 1/4" male contact terminals • 1.75" x 1" x 1.75" • 1 Year Warranty

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov