



SKU # RSPNPH8

Part # 1006924

Description

H8 PNP Series Plug N Play Super LUX LED OEM Replacement Bulb Kit

Categories LED Headlight Conversions

Sub-Categories PNP SERIES LED Headlight Bulbs

UPC 817999025705

Unit of Measure PR

Related Skus:

RSCAS003

Cross Sell Skus:

RSIKIT,RSUKIT,RS8PRGBW

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

PNP Series Bulbs

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

9-32VDC

Current Draw

Wattage

Chip Type

FCiP

IP Rating

IP67

LUX

5,480lx/Kit

Kelvin (ColorTemperature)

6,000K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

4,420lm/kit

Beam Pattern

N/A



Product Information

This new technology from Race Sport Lighting brings direct fit LED replacement driving lights to the market that have the same size base, length, and overall size as the halogen bulbs they are replacing, but with the power and efficiency of LED. There are no fans or drivers necessary on these bulbs. Simply un-plug your halogen bulbs and plug these in and go. • One Piece Die-cast Bulb Body • Superior heat dissipation and thermal conductivity • Increase driving distance 2-3 times over halogen bulbs • 9V-32V operating range • Built-in drivers, making it 100% Plug N Play when replacing halogen bulbs • Same size as Halogen bulbs it replaces - No oversized issues • Uses FCiP Ultra-high luminous bulbs for High Power output • Rated 1,900 LUX/bulb or 3,800 LUX/kit (RAW Measured LUX @ 1FT is 2,740lx/bulb or 5,480lx/kit) • Rated 2,000 MAX Lumens per bulb, 4,000 Max Lumens per set of bulbs (RAW Measured LUMEN is 2,210lm/bulb or 4,420lm/kit) • 1 Year Warranty • NOTE - Newe

Est. Labor 0.5 Hours

Gross Weight 1.00 **Width** 2.25

Net Weight 1.00 **Height** 3.00

DIM Weight 0.15 **Depth** 3.00