



SKU # RSPNPH9

Part # 1006921

Description

H9 PNP Series Plug N Play Super LUX LED OEM Replacement Bulb Kit

Categories LED Headlight Conversions

Sub-Categories PNP SERIES LED Headlight Bulbs

UPC 817999025712 Unit of Measure PR

Related Skus: RSCAS003

Cross Sell Skus: RSIKIT,RSUKIT,RS8PRGBW

Condition New Manufacturer Race Sport Lighting EZ Category PNP Series Bulbs

Harmonization Code 8512.20.2080 Universal YES Life Expectancy 50,000 hours

SEMA Product Headlight Conversion Kit Part Type ID 12571

Reverse Polarity Headlight Conversion Kit Operating Voltage 9-32VDC Current Draw

Wattage Chip Type FCiP IP Rating IP67 LUX 5,480lx/Kit

Kelvin (ColorTemperature) 6,000K Universal or Vehicle Specific Universal

Made In China Warranty 1 year Lumens 4,420lm/kit Beam Pattern N/A



Product Information

This new technology from Race Sport Lighting brings direct fit LED replacement driving lights to the market that have the same size base, length, and overall size as the halogen bulbs they are replacing, but with the power and efficiency of LED. There are no fans or drivers necessary on these bulbs. Simply un-plug your halogen bulbs and plug these in and go. • One Piece Die-cast Bulb Body • Superior heat dissipation and thermal conductivity • Increase driving distance 2-3 times over halogen bulbs • 9V-32V operating range • Built-in drivers, making it 100% Plug N Play when replacing halogen bulbs • Same size as Halogen bulbs it replaces - No oversized issues • Uses FCiP Ultra-high luminous bulbs for High Power output • Rated 1,900 LUX/bulb or 3,800 LUX/kit (RAW Measured LUX @ 1FT is 2,740lx/bulb or 5,480lx/kit) • Rated 2,000 MAX Lumens per bulb, 4,000 Max Lumens per set of bulbs (RAW Measured LUMEN is 2,210lm/bulb or 4,420lm/kit) • 1 Year Warranty • NOTE - Newe

Est. Labor	0.5 Hours		
Gross Weight	1.00	Width	2.25
Net Weight	1.00	Height	3.00
DIM Weight	0.15	Depth	3.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov