



SKU # RS-12W4LED-FM

Part # 1003757

Description

Flush Mount 12W 4 LED High-Powered 3x3 LED Spot Light



Categories Powersports, Agricultural, LED Spots and Auxiliary Lighting

Sub-Categories

STREET Series LED Spot Lights, STREET Series LED Spot Lights, Street Series Spot Lights & Accessories

UPC 812867023401

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Street Series Aux Spots

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Auxiliary Light

Part Type ID 1005

Reverse Polarity

Auxiliary Light

Operating Voltage

9-24VDC

Current Draw

2.5A

Wattage

12-Watts

Chip Type

IP Rating

IP67

LUX

1,500LUX

Product Information

Our Flush Mount LED Spots make for the perfect fit to your vehicle, taking up little to no space while offering comparable light output to our cube style spots. • Special optics project Light further than the competition • 12W/1,500 LUX (3W per diode) • 50,000+ hour LED lifespan • Instant On/Off - No Warm Up • RoHS Compliant • Sturdy Cast Aluminum Housing • Durable Polycarbonate Lens • 12 Watt Spot features 4 LEDs • 2.5 Amps • 3 Year Warranty

Est. Labor

1 Hours

Gross Weight

1.40

Width

5.00

Net Weight

1.40

Height

4.50

DIM Weight

0.97

Depth

6.00

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

3 year

Lumens

Beam

Pattern

Spot

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com