



SKU # RS-16MM-LEDG

Part # 1003764

Description

16mm Flush Mount LED Momentary Switch (GREEN) (Sold Each) - Comes pre-wired with voltage regulation resistor.

Categories Auto Interior & Exterior, LED Switches

Sub-Categories LED Switches, Momentary Anti-Vandal Switches

UPC 811712020572

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Flush Mount LED Switches

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Accessory Switch

Part Type ID 48173

Reverse Polarity

Accessory Switch

Operating Voltage

12VDC

Current Draw

15A

Wattage

N/A

Chip Type

N/A

IP Rating

IP67

LUX

N/A

Product Information

Great for push-to-start or any accessory that only requires a momentary change to a circuit, these 12V Illuminated LED Momentary Push Button Switches are an economical, attractive option for your dash. They come in chrome with an assortment of colorful LED rings to suit anyone's style. • Momentary push button • Anti-vandal style switch • Available in Red, Green, Blue, Yellow, and White • 15 Amps @ 12V • 1 Year Warranty

Est. Labor

Hours

Gross Weight

0.10

Width

3.00

Net Weight

0.10

Height

5.00

DIM Weight

0.11

Depth

1.00

Kelvin (ColorTemperature)

Green

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

N/A

Beam Pattern

N/A

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com

