



SKU # RS-27W-S-2

Part # 1003781

Description

Street Series 4in Square LED Work Spot Light 27W/1,755LM (Pair)

Categories Truck, Powersports, Agricultural, LED Spots and Auxiliary Lighting

Sub-Categories

Auxiliary Spot & Floods, STREET Series LED Spot Lights, STREET Series LED Spot Lights, Street Series Spot Lights & Accessories

UPC 817363014922

Unit of Measure PR

Related Skus:

Cross Sell Skus:

RSTP016

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Street Series Aux Spots

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product Auxiliary Light

Part Type ID 1005

Reverse Polarity

Auxiliary Light

Operating Voltage

9-24VDC

Current Draw

Wattage

27-Watts

Chip Type

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

3 year

Lumens

1,755lm

Beam

Pattern



Product Information

Great as an off road work light, these 4" Square LED spots let out almost 2,000 Lumens of light output, more than enough for any purpose. • 27W/1,755LM (3W per diode) • 50,000 hour lifetime • 6,500 Kelvin color • Combination spot and flood optics • Durable spotlights, built to last • 3 year limited Warranty • Also sold individually

Est. Labor

1 Hours

Gross Weight

3.40

Width

10.00

Net Weight

3.40

Height

3.00

DIM Weight

1.29

Depth

6.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov