



SKU # RS-281-4LED-BA

Part # 1003895

Description

(4) L.E.D Grill Strobe Light Kit - Blue/Amber - Complete Kit with Hardware



Categories Strobe Lighting Kits

Sub-Categories LED Strobe Light Kits

UPC 817999024005

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

LED Strobe Kit

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Strobe Light Kit

Part Type ID 17809

Reverse Polarity

Strobe Light Kit

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

IP67

LUX

Product Information

This LED grille strobe light kit allows you to easily increase visibility of their vehicle, with easy to mount low profile LED strobes. Compatible with: All vehicles and devices equipped with a 12 Volt DC power source. Features: • Waterproof rated and ready for exterior mounting • Low profile for easy mounting on any vehicle • Various Selectable Strobe Patterns Kit Contains: (4) LED Light Block with Mounting Brackets (4) 8ft (244cm) Extension Wire with Connectors (1) Controller Module Screws and Accessories Installation Guide • 1 Year Warranty

Est. Labor

Hours

Gross Weight

4.20

Width

5.00

Net Weight

4.20

Height

5.00

DIM Weight

2.16

Depth

12.00

Kelvin (ColorTemperature)

Blue/Amber

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com