



SKU # RS-2P16MM-LEDY

Part # 1003624

Description

16mm LED 2-Position On/Off Switch (Yellow) - Chrome Finish



Categories Auto Interior & Exterior, LED Switches

Sub-Categories LED Switches, 2-Position Anti-Vandal Switches

UPC 811712021760

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Flush Mount LED Switches

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product

Accessory Switch

Part Type ID

48173

Reverse Polarity

Accessory Switch

Operating Voltage

12VDC

Current Draw

15A

Wattage

N/A

Chip Type

N/A

IP Rating

IP67

LUX

N/A

Product Information

Whether you need a switch for a light bar or anything else in your vehicle, these 12V Illuminated LED 2-Position Switches are an economical option for integrating additional lighting or 12V equipment into your vehicle with ease. They come in chrome or black with an assortment of colorful LED rings to suit anyone's style. • 2-Position On/Off • Anti-vandal style switch • Available in Black or Chrome with Red, Green, Blue, Yellow, and White rings • 1 Year Warranty

Est. Labor

Hours

Gross Weight

0.10

Width

3.00

Net Weight

0.10

Height

5.00

DIM Weight

0.11

Depth

1.00

Kelvin (ColorTemperature)

Yellow

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

N/A

Beam Pattern

N/A

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com