



**SKU # RS-C3069SM6-B**

**Part # 1004284**

Description

6-LED Blue IP68 Surface Mount Light Head w/ Strobe

**Categories** Agricultural, Strobe Lighting Kits, Strobe Lighting Kits

**Sub-Categories**

Surface Mount LED Strobe Marker Lights, Surface Mount Marker Lights, Marker Lights

**UPC** 812867029526

**Unit of Measure** EA

**Related Skus:**

RSMSPLATE

**Cross Sell Skus:**

**Condition**

New

**Manufacturer**

Race Sport Lighting

**EZ Category**

LED Strobe Markers

**Harmonization Code**

8512.20.2080

**Universal**

YES

**Life Expectancy**

**SEMA Product** Strobe Light Kit

**Part Type ID** 17809

**Reverse Polarity**

Strobe Light Kit

**Operating Voltage**

**Current Draw**

**Wattage**

**Chip Type**

**IP Rating**

**LUX**

**Kelvin (ColorTemperature)**

Blue

**Universal or Vehicle Specific**

Universal

**Made In**

China

**Warranty**

1 year

**Lumens**

**Beam**

Pattern



**Product Information**

Surface Mount, Quality Throughout • Compact surface mount directional LED strobes for emergency or law enforcement vehicles • 11 strobe patterns for multipurpose use • IP68 rated for marine use • Small black housings allow for discreet application • Perfect for marked or unmarked police cars, ambulances, fire trucks, rescue vehicles, patrol boats, tow trucks, snow plows, or tractors • 1 Year Warranty

**Est. Labor**

Hours

**Gross Weight**

0.20

**Width**

1.50

**Net Weight**

0.20

**Height**

5.50

**DIM Weight**

0.09

**Depth**

1.50

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)