



SKU # RS-C3069SM6-R

Part # 1004285

Description

6-LED IP68 Surface Mount Light Head w/ Strobe - RED Color

Categories Agricultural, Strobe Lighting Kits, Strobe Lighting Kits

Sub-Categories

Surface Mount LED Strobe Marker Lights, Surface Mount Marker Lights, Marker Lights

UPC 812867029519

Unit of Measure EA

Related Skus:

RSMSPLATE

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

LED Strobe Markers

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Strobe Light Kit

Part Type ID 17809

Reverse Polarity

Strobe Light Kit

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

Red

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern



Product Information

Surface Mount, Quality Throughout • Compact surface mount directional LED strobes for emergency or law enforcement vehicles • 11 strobe patterns for multipurpose use • IP68 rated for marine use • Small black housings allow for discreet application • Perfect for marked or unmarked police cars, ambulances, fire trucks, rescue vehicles, patrol boats, tow trucks, snow plows, or tractors • 1 Year Warranty

Est. Labor

Hours

Gross Weight

0.20

Width

1.50

Net Weight

0.20

Height

5.50

DIM Weight

0.09

Depth

1.50

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov