



SKU # RS-CREE-40BARHD

Part # 1004304

Description

42in Heavy Duty Series CREE Combo Bar 210W/16,800LM

Categories Truck, Powersports, Agricultural, Jeep, LED Light Bars

Sub-Categories

LED Light Bars, Heavy Duty PROFESSIONAL Series Dual Row LED Light Bars - Lifetime Warranty, Heavy Duty PROFESSIONAL Series Dual Row LED Light Bars - Lifetime Warranty, Heavy Duty Series Dual Row LED Light Bars, Heavy Duty Series Dual Row Light Bars

UPC 811712024204

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

HD Series Dual Row Light Bars

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

50,000 hours

SEMA Product

Light Bar

Part Type ID

1069

Reverse Polarity

Light Bar

Operating Voltage

12-32VDC

Current Draw

19A

Wattage

210-Watts

Chip Type

CREE

IP Rating

IP68

LUX

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

Lifetime

Lumens

16,800lm

Beam Pattern

Combo



Product Information

Premium light bars for serious off-roading and demanding situations. These bars will take punishment and never let you down • 240W/16,800 LM (3W per diode) • Combination Flood/Spot Optics • 19 Amps • 50,000 hour lifetime • 6,500 Kelvin color • 12V-32V capable • IP68 Waterproof Rated • Bar Measures 42" End to End w/ Brackets • Lens Measures 40" End to End • Mount to Mount measurement is 45" • Super efficient LED driver • Special optics improve light projection • Perfect for off-road, emergency, and public use • Lifetime Warranty

Est. Labor

Hours

Gross Weight

16.50

Width

43.00

Net Weight

16.50

Height

5.25

DIM Weight

8.53

Depth

5.25

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com