



## SKU # RS-CREE-50BARHD

Part # 1004305

### Description

52in Heavy Duty Series CREE Combo Bar 260W/21,000LM



**Categories** Truck, Powersports, Agricultural, Jeep, LED Light Bars

### Sub-Categories

LED Light Bars, Heavy Duty PROFESSIONAL Series Dual Row LED Light Bars - Lifetime Warranty, Heavy Duty PROFESSIONAL Series Dual Row LED Light Bars - Lifetime Warranty, Heavy Duty Series Dual Row LED Light Bars, Heavy Duty Series Dual Row Light Bars

**UPC** 811712024211

**Unit of Measure** EA

**Related Skus:**

**Cross Sell Skus:**

### Condition

New

### Manufacturer

Race Sport Lighting

### EZ Category

HD Series Dual Row Light Bars

### Harmonization Code

8512.20.2080

### Universal

YES

### Life Expectancy

50,000 hours

**SEMA Product** Light Bar

**Part Type ID** 1069

### Reverse Polarity

Light Bar

### Operating Voltage

12-32VDC

### Current Draw

23.8A

### Wattage

260-Watts

### Chip Type

CREE

### IP Rating

IP68

### LUX

### Est. Labor

Hours

### Gross Weight

19.60

### Width

53.00

### Net Weight

19.60

### Height

5.25

### DIM Weight

10.51

### Depth

5.25

### Kelvin (ColorTemperature)

6,500K

### Universal or Vehicle Specific

Universal

### Made In

China

### Warranty

Lifetime

### Lumens

21,000lm

### Beam Pattern

Combo

### Product Information

Premium light bars for serious off-roading and demanding situations. These bars will take punishment and never let you down • 300W/21,000 LM (3W per diode) • Combination Flood/Spot Optics • 23.8 Amps • 50,000 hour lifetime • 6,500 Kelvin color • 12V-32V capable • IP68 Waterproof Rated • Bar Measures 52" End to End w/ Brackets • Lens Measures 50" End to End • Mount to Mount measurement is 55" • Super efficient LED driver • Special optics improve light projection • Perfect for off-road, emergency, and public use • Lifetime Warranty