



SKU # RS-H10-LED-LAMP-PR

Part # 1004580

Description

H10 High-Powered Projector LED DRL Bulbs (Pair)



Categories Auto Interior & Exterior, LED Replacement Bulbs

Sub-Categories LED Replacement Bulbs, Other LED Replacement Bulbs

UPC 812867027980

Unit of Measure PR

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Z-Closeout

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product

Daytime Running Light

Part Type ID

10348

Reverse Polarity

Daytime Running Light

Operating Voltage

12-24VDC

Current Draw

Wattage

Chip Type

IP Rating

LUX

Product Information

- 1 Year Warranty • Cost effective aesthetically pleasing DRL & Fog light upgrade • 360° light output with durable projection lenses offering you 700+ Lumens of light output
- Utilizing 5050SMD and Cree technology this is the perfect upgrade to your standard halogen bulbs.

Est. Labor

Hours

Gross Weight

0.10

Width

5.00

Net Weight

0.10

Height

7.00

DIM Weight

0.25

Depth

1.00

Kelvin (ColorTemperature)

White

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com