



SKU # RS-SRWRAP-200W

Part # 1004795

Description

SINGLE ROW Series 40in CREE Wrap Around Series 20,000lm COMBO LED Light Bar



Categories Truck, LED Light Bars

Sub-Categories LED Light Bars, Wraparound Light Bars

UPC 812867024194

Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Single Row Wrap Around Light Bar

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Light Bar

Part Type ID 1069

Reverse Polarity

Light Bar

Operating Voltage

12VDC

Current Draw

15.87A

Wattage

200-Watts

Chip Type

CREE

IP Rating

LUX

Product Information

Keep yourself ahead of the curve with our wide angle Wrap Around Series Light Bars • Wrap Around light bars contour beautifully to your car's bumper or roof • 200W/20,000LM (10W per diode) • 15.87 Amps • 50,000 hour lifetime • 6,500 Kelvin color • Curved design increases angle of light dispersion to 180° • Combination flood and spot optics • Bar Height: 3.3" (84mm) • Mounted Height (Varies, Dependent on Angle): 3.75"-4.25" (95mm-108mm) • 42" Length End to End w/ Brackets • 40" Lens Length End to End • 45" Length Mount to Mount • Durable, heavy duty bars, built to last • 1 Year Warranty

Est. Labor

Hours

Gross Weight

11.80

Width

5.00

Net Weight

11.80

Height

47.00

DIM Weight

11.83

Depth

7.00

Kelvin (ColorTemperature)

6,500K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

20,000lm

Beam

Pattern

Combo

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com