



SKU # RS-T10-5-5050CAN-W

Part # 1004814

Description

T10 / 194 5050 CANBUS LED 5-Chip Version (White) (Pair)



Categories Auto Interior & Exterior, Motorcycle, LED Replacement Bulbs

Sub-Categories

LED Replacement Bulbs, LED Moto Replacement Signal Bulbs, 5050 Canbus Series
LED Replacement Bulbs

UPC 811712023511

Unit of Measure PR

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

5050 CANBUS LED Bulbs

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product License Plate Light

Part Type ID 2816

Reverse Polarity

License Plate Light

Operating Voltage

12-24VDC

Current Draw

Wattage

Chip Type

IP Rating

LUX

Product Information

Step it up and replace your stock bulbs with our professional grade 5050 LED replacement bulbs for brighter, crisper illumination Race Sport Lighting's LED Replacement Bulbs are available in a variety of bases and colors for virtually any application, and are the perfect solution to upgrade your interior or exterior automotive lighting • 1 Year Warranty Cross Reference for T10 (194) = T10, T13, 147, 152, 158, 159, 161, 168, 184, 192, 193, 259, 280, 285, 447, 464, 555, 585, 655, 656, 657, 1250, 1251, 1252, 2450, 2652, 2852, 2921, W2W, W5WB, 579, 2886x, 175

Est. Labor

0.1 Hours

Gross Weight

0.10

Width

3.25

Net Weight

0.10

Height

5.00

DIM Weight

0.03

Depth

0.25

Kelvin (ColorTemperature)

White

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com