



SKU # RS-T10-W-5050

Part # 1006713

Description

T10 194 LED Auto Replacement Bulbs (Pair) 5050 Diode Technology - COLOR WHITE



Categories LED Replacement Bulbs

Sub-Categories 5050 Series LED Replacement Bulbs

UPC 811712020350

Unit of Measure PR

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

5050 LED Replacement Bulbs

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product License Plate Light

Part Type ID 2816

Reverse Polarity

License Plate Light

Operating Voltage

12-24VDC

Current Draw

Wattage

Chip Type

IP Rating

LUX

Product Information

Cross Reference for T10 (194) = T10, T13, 147, 152, 158, 159, 161, 168, 184, 192, 193, 259, 280, 285, 447, 464, 555, 585, 655, 656, 657, 1250, 1251, 1252, 2450, 2652, 2852, 2921, W2W, W5WB, 579, 2886x, 175

Est. Labor

Hours

Gross Weight

0.20

Width

5.00

Net Weight

0.20

Height

3.00

DIM Weight

0.05

Depth

0.50

Kelvin (ColorTemperature)

White

Universal or Vehicle Specific

Universal

Made In

CN

Warranty

1 year

Lumens

Beam Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com