



SKU # RS-TBDL270KIT-A

Part # 1004846

Description

Stealth LED 19 Pattern Strobe Light Heads (Amber) (Sold as Pair)

Categories Commercial, Agricultural, Strobe Lighting Kits

Sub-Categories

LED Strobe Light Kits, LED & Halogen Strobe Light Kits, LED Strobe Light Kits

UPC 811712027687

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

LED Strobe Kit

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product

Strobe Light Bulb

Part Type ID

17811

Reverse Polarity

Strobe Light Bulb

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

Amber

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam Pattern



Product Information

Features: • Each unit consists of six high intensity LEDs • Slim in-line driver/flasher; no separate controller required • 19 selectable flash patterns • Last pattern memory recall • Synchronization between multiple units • Easily replaces standard halogen hide-a-way lamps with existing 1" hole • Versatile application for surface mounting design or internal mounting within light assemblies • Weatherproof ready for exterior mounting (not submersible) • 1 Year Warranty Kit Contains: (2) LED Hide-A-Way Strobe (2) Rubber Gasket Screws

Est. Labor

Hours

Gross Weight

1.60

Width

7.00

Net Weight

1.60

Height

6.50

DIM Weight

2.46

Depth

7.50

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov