



SKU # RS-TBDL270KIT-W

Part # 1004847

Description

Stealth LED 19 Pattern Strobe Light Heads (White) (Sold as Pair)

Categories Commercial, Agricultural, Strobe Lighting Kits

Sub-Categories

LED Strobe Light Kits, LED & Halogen Strobe Light Kits, LED Strobe Light Kits

UPC 811712027670 Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition	Manufacturer	EZ Category	
New	Race Sport Lighting	LED Strobe Kit	
Harmonization Code	Universal	Life Expectancy	
8512.20.2080	YES		
SEMA Product	Part Type ID	17811	
Strobe Light Bulb			
Reverse Polarity	Operating Voltage	Current Draw	
Strobe Light Bulb			
Wattage	Chip Type	IP Rating	LUX

Kelvin (ColorTemperature)		Universal or Vehicle Specific	
White		Universal	
Made In	Warranty	Lumens	Beam Pattern
China	1 year		



Product Information

Features:

- Each unit consists of six high intensity LEDs
- Slim in-line driver/flasher; no separate controller required
- 19 selectable flash patterns
- Last pattern memory recall
- Synchronization between multiple units
- Easily replaces standard halogen hide-a-way lamps with existing 1” hole
- Versatile application for surface mounting design or internal mounting within light assemblies
- Weatherproof ready for exterior mounting (not submersible)
- 1 Year Warranty

Kit Contains: (2) LED Hide-A-Way Strobe (2) Rubber Gasket Screws

Est. Labor	Hours		
Gross Weight	1.60	Width	7.00
Net Weight	1.60	Height	6.50
DIM Weight	2.46	Depth	7.50

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov