



SKU # RS-U30LEDC13.75-W

Part # 1004852

Description

13.75 inch White LED Ultra Bright Accent Weatherproof Light Bar Strip with Aluminum Mounting Channel Ultra Series - USA Made Race Sport Lighting



Categories Interior/Exterior Accent LED

Sub-Categories Ultra Series Accent Bars

UPC 811712021036 Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition New Manufacturer Race Sport Lighting EZ Category LED Accent Lighting

Harmonization Code 8512.20.2080 Universal YES Life Expectancy

SEMA Product Auxiliary Light Part Type ID 1005

Reverse Polarity Auxiliary Light Operating Voltage Current Draw

Wattage Chip Type IP Rating LUX

Product Information

Race Sport Lighting's Ultra Series LED accent bars are a durable, ultra-bright lighting solution, ready to take a beating in any exterior automotive lighting application • 13.75” Long • Polished aluminum channel with chrome tips • Great for all exterior applications like truck bed lighting or courtesy lights • Mounts with 3M tape or screw-mount metal channel • IP68 Waterproof Rated • 30 LEDs/m (1 1/4" spacing) or 60 LEDs/m (5/8" spacing) • High lumen output with low heat • Wide dispersion of light • 1 Year Warranty

Est. Labor	Hours		
Gross Weight	0.10	Width	4.00
Net Weight	0.10	Height	17.00
DIM Weight	0.12	Depth	0.25

Kelvin (ColorTemperature) White Universal or Vehicle Specific Universal

Made In USA Warranty 1 year Lumens Beam Pattern

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

www.racesportinc.com