



SKU # T10RESISTOR

Part # 1005991

Description

T10 Base Resistor In-line (Pair)

Categories

Auto Interior & Exterior, HID & LED Headlights, LED Headlight Conversions

Sub-Categories

LED Replacement Bulbs, HID Interface Solutions, LED Interface Solutions

UPC 811712022835

Unit of Measure PR

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

Resistors

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

SEMA Product Bulb Resistor

Part Type ID 17750

Reverse Polarity

Bulb Resistor

Operating Voltage

Current Draw

Wattage

Chip Type

IP Rating

LUX

Kelvin (ColorTemperature)

N/A

Universal or Vehicle Specific

Universal

Made In

China

Warranty

1 year

Lumens

Beam

Pattern



Product Information

T10 load resistors stop the computer from faulting when aftermarket T10 LED bulbs are installed, preventing unwanted error and warning lights • In-line resistor with T10 style connector • Sold in pairs • 1 Year Warranty

Est. Labor

Hours

Gross Weight

0.10

Width

5.50

Net Weight

0.10

Height

3.00

DIM Weight

0.06

Depth

0.50