

# ENDLESS ROUNDUP® ROUNDSLINGS

## ENDLESS (ENR)

Endless RoundUp™ RoundSlings are the most basic roundsling, yet they offer great versatility. Endless roundslings may be used in a vertical, choker or basket type hitch.

### ADVANTAGES:

- Reduce cost with less total rigging weight
- Easy handling and storage
- Reduce risk of back and hand injuries

- Cover abrasion will not reduce capacity
- Provides a strong grip on loads
- Provides a tighter choke with an easier release
- Capacities are color coded

### HOW TO ORDER:

Part Number and Length

(Sling Length: Bearing Point to Bearing Point)

Example: ENR2 X 20 FT

### ENDLESS ROUNDSLING CAPACITY CHART

Colour	Part Number	Vertical	Choker	Basket	Minimum Length	Approx. Diameter	Approx. WT / FT
PURPLE	ENR1	2600	2100	5200	3'	.625"	0.3 LB
GREEN	ENR2	5300	4200	10600	3'	.875"	0.4 LB
YELLOW	ENR3	8400	6700	16800	3'	1.125"	0.5 LB
TAN	ENR4	10600	8500	21200	3'	1.125"	0.6 LB
RED	ENR5	13200	10600	26400	3'	1.375"	0.8 LB
WHITE	ENR6	16800	13400	33600	6'	1.375"	0.9 LB
BLUE	ENR7	21200	17000	42400	6'	1.625"	1.3 LB
ORANGE	ENR8	25000	20000	50000	6'	1.750"	1.6 LB
ORANGE	ENR9	31000	24800	62000	6'	2.125"	2.0 LB
ORANGE	ENR10	40000	32000	80000	6'	2.350"	2.6 LB
ORANGE	ENR11	53000	42400	106000	8'	3.150"	3.4 LB
ORANGE	ENR12	66000	52800	132000	8'	3.950"	4.3 LB
ORANGE	ENR13	90000	72000	180000	8'	4.800"	5.9 LB
ORANGE	ENR14	100000	80000	200000	8'	5.520"	6.8 LB

### LARGER SIZES AVAILABLE



*\*Before ordering slings that are going to be used in a chemically active environment, contact Cargo Lift® Customer Service, to recommend the right sling for the right usage.*

