

### Features

- **CONVENIENT** -  
3.6 horsepower (12-volt) DC motor.
- **EFFICIENT** -  
Line speed of 3.9 feet per minute with a full load, and 15.7 feet per minute with no load.
- **COMPLETE SETUP** -  
Included mounting channel, roller fairlead, wiring kit with contactor and mini-rocker handlebar switch.
- **HASSLE-FREE** -  
The roller fairlead creates a safe and smooth pull with the dependable 85-foot galvanized, super-duty aircraft cable.



### Specifications

<b>RATED PULL</b>	10,000 lb. (4536 kg)
<b>GEAR REDUCTION RATIO</b>	216:1
<b>MOTOR</b>	3.6 HP (2.7kW) (12V DC)
<b>DUTY CYCLE</b>	Intermittent use only
<b>DRUM SIZE</b>	2.5 in. x 8.8 in
<b>CABLE/ROPE TYPE</b>	Galvanized Steel
<b>CABLE/ROPE DIMENSIONS</b>	85 ft. x 3/8 in.
<b>BOLT PATTERN</b>	10 in. x 4.5 in.

Champion's Truck/SUV winch kit with cover has a 10,000-lb. rated line pull, a gear reduction ratio of 216:1, and a remote control to make your experience with this winch even easier. With a tough 3.6-horsepower (12-volt) DC motor, this is your perfect heavy-duty tool.

### Inside the box

OPERATOR'S MANUAL  
WINCH  
MOUNTING CHANNEL

MINI-ROCKER SWITCH  
CABLES AND CONTACTOR  
ROLLER FAIRLEAD

\*Specifications, descriptions and illustrations are subject to change without notice.

**PACKAGE (gross)**  
Weight: 92.5 lb.  
Size: 26.8 x 13 x 12.6 in.

**PRODUCT (net)**  
Weight: 85 lb.  
Size: 21.9 x 10.5 x 5.6 in.

**CHAMPION POWER EQUIPMENT, INC.**  
12039 Smith Ave., Santa Fe Springs, CA 90670, USA  
www.championpowerequipment.com