

Digital Thermometer

Model: DT392, DT392-ES (Spanish)

Easy-to-read front display. One-button operation. ABS sheath can be used as handle extension.



Features	One-button operation, on/off switch
Certification	NSF [®] Certified, WEEE, CE
Antimicrobial Protection	BioCote [®]
Measurement Range	-50 to +392°F/-45 to +200°C
Unit of Measure	°F/°C
Accuracy	±2°F
Response Time	6-8 second response
On/Off	On/off switch
Auto-off	Auto-off after 10 minutes
Housing Material	Food-safe ABS
Display Material	LCD
Display Size	0.875 W x 0.375 H (in)/2.2 W x 1.0 H (cm)
Probe Type	Thermistor
Probe Material	304 stainless steel
Probe Length	5"/12.7 cm stem
Probe Diameter	3 mm tip
Resolution	0.1°F/0.1°C
Casing	Sheath
Temperature Guide	USDA safe food temperature guide on sheath
Mounting	Pocket clip
Operating Range	32 to 104°F/0 to 40°C/≤90% RH
Battery	1.5V IEC LR44 alkaline button, included
Dimensions	1.25 W x 5.625 H x 1.125 D (in)/3.2 W x 14.3 H x 2.9 D (cm)
Weight	0.8 oz / 22.7 g (including battery)
Warranty	5-Year Limited Warranty