

Digital Candy Thermometer

Model: DTC450

With seven preprogrammed candy stages and one all-purpose temperature setting, this thermometer provides easy control over candy and other high temperatures. Dual progress display and alert warnings before, during, and at key temperatures in the candy range.



Features	Preprogrammed, programmable, dual progress display, alert, auto-off after 1 hour, heat shield
Certification	WEEE, CE
Measurement Range	14 to 450°F/-10 to +232°C
Unit of Measure	°F/°C
Accuracy	±1.5°F
Response Time	1 second
Alert/Alarm	Audio/visual pre-alert, target alert and over-alert for all stages
On/Off	On – mode button
Auto-off	Auto-off after 1 hour
Housing Material	ABS plastic, 304 stainless steel stem
Display Material	LCD
Display Size	0.875 W x 0.875 H (in)/2.2 W x 2.2 H (cm)
Probe Type	Thermistor
Probe Material	304 stainless steel
Probe Length	8.25"/20.96 cm stem
Resolution	0.1°F/0.1°C
Vessel Clip	Adjustable stainless steel clip AD-L
Casing	Sheath
Mounting	Pocket clip
Operating Range	-4°F to +122°F/-20°C to +50°C
Battery	Two 1.5V IEC LR44 alkaline button batteries, included
Dimensions	1.25 W x 10.875 H x 0.625 D (in)/2.5 W x 27.62 H x 1.6 D (cm)
Weight	4.9 oz / 138 g (including batteries)
Warranty	5-Year Limited Warranty
Replacement Parts	AD-L