

Probe Thermometer

Model: DTP392, DTP392-ES (Spanish)

Instant readout of internal food temperature during cooking. 5½-inch stainless steel probe. 3-foot sensor cable. Audio/visual alarm. Magnet or stand mounting.



Features	Dual progress display, big digit, audio/visual, sliding mode switch, on/off switch
Certification	WEEE, CE
Measurement Range	32 to 392°F/0 to 200°C
Unit of Measure	°F/°C
Heat Resilience	Probe: 392°F/200°C, high heat sensor cable: 428°F/220°C for 3 hours
Water Resilience	Probe able to be submerge in 1 inch water for 30 minutes, not including probe-sensor cable junction
Alert/Alarm	Audio/visual alert
On/Off	On/off switch
Housing Material	Food-safe ABS plastic
Display Material	LCD
Display Size	1.75 W x 0.75 H (in)/4.4 W x 1.9 H (cm)
Probe Type	Thermistor
Probe Material	304 stainless steel
Probe Length	5.5"/14.0 cm probe / 3'/91.4 cm sensor cable
Resolution	1°F/1°C
Mounting	Magnet and stand
Operating Range	32 to 104°F/0 to 40°C/≤90% RH
Battery	1.5V AAA IEC LR03 alkaline battery, included
Battery Life	1 year (working 2 hours/day)
Dimensions	3.25 W x 2.375 H x 1 D (in)/8.3 W x 6.0 H x 2.5 D (cm)
Weight	3.9 oz / 110.6 g (including battery)
Warranty	5-Year Limited Warranty
Optional Accessories	Adjustable stainless steel clip AD-P
Replacement Parts	AD-DTP392