



Waterproof Thin Tip Thermometer

Model: DTTW572

This full-featured ergonomic thermometer offers an IPX7 waterproof rating, 3.5-inch stem, 1.5 mm thin tip, fast 4-second response and one-button field calibration. With hold and max/min modes, the 180° rotating display makes this thermometer easy-to-read in any position.

Waterproof Thin Tip Thermometer

Model: DTTW572

This full-featured ergonomic thermometer offers an IPX7 waterproof rating, 3.5-inch stem, 1.5 mm thin tip, fast 4-second response and one-button field calibration. With hold and max/min modes, the 180° rotating display makes this thermometer easy-to-read in any position.



Features	180° rotating display, hold mode, max/min mode, on/off button
Certification	NSF [®] Certified, WEEE, CE
Antimicrobial Protection	BioCote [®]
Measurement Range	-40 to +572°F/-40 to 300°C
Unit of Measure	°F/°C
Accuracy	-40 to +392°F/-40 to +200°C: ±0.7°F/±0.4°C; above 392°F/200°C: ±1.8°F/±1°C (@ ambient temperature 73°F: ±3.6°F/23°C: ±2°C)
Calibration	Field calibration
Heat Resilience	High heat
Water Resilience	IPX7: protected from water up to 3 feet/1 meter for 30 minutes
Response Time	4 second response
On/Off	On/off button
Auto-off	Auto-off after 10 minutes (disabled at ≥104°F/40°C)
Housing Material	Food-safe ABS
Display Material	LCD
Display Size	0.94 W x 0.43 H (in)/2.4 W x 1.1 H (cm)
Probe Type	Thermistor
Probe Material	304 stainless steel
Probe Length	3.5"/8.9 cm stem
Probe Diameter	1.5 thin tip
Resolution	0.1°F/0.1°C
Casing	Sheath
Mounting	Pocket clip and hook; optional magnet
Temperature Guide	On thermometer
Operating Range	32 to 104°F/0 to 40°C/≤90% RH
Battery	Two 1.5V IEC LR44 alkaline button batteries included
Battery Life	10 months (3 times/day, 5 sec/time)
Dimensions	0.87 W x 7.24 H x 0.89 D (in)/2.22 W x 18.4 H x 2.25 D (cm)
Weight	1.8 oz / 45 g (including battery)
UPC	0 18436 00507 0
Warranty	5-Year Limited Warranty

