

# Beverage & Frothing Thermometer – 5" Stem

**Model: IRB220-F, IRB220-F-C (Celsius),**

Color-coded target range indication. 1½-inch magnified dial. 5-inch stem. Durable 304 stainless steel. Exclusive adjustable stainless steel vessel clip for small pitchers. Calibration tool and pocket clip on ABS sheath with BioCote<sup>®</sup>. Safe for commercial dishwashers.



Features	Target range indication
Certification	NSF <sup>®</sup> Certified
Antimicrobial Protection	BioCote <sup>®</sup>
Measurement Range	0 to 220°F/-18 to +104°C
Unit of Measure	°F/°C
Accuracy	±2°F
Calibration	Field calibration
Water Resilience	Safe for commercial dishwashers
Response Time	15 second response (approximate)
Housing Material	304 stainless steel
Display Material	Shatterproof lens
Display Size	1.5"/3.8 cm magnified dial
Probe Type	Bimetal
Probe Material	304 stainless steel
Probe Length	5"/12.7 cm stem
Probe Diameter	3 mm tip
Resolution	2°F/1°C
Vessel Clip	Adjustable stainless steel clip AD-F
Casing	Sheath
Mounting	Pocket clip
Dimensions	1.5 W x 5.5 H x 1.5 D (in)/3.8 W x 14.0 H x 3.8 D (cm)
Weight	1.0 oz / 28.3 g
Warranty	5-Year Limited Warranty
Optional Accessories	AD-F