

# Ovenproof Meat Thermometer

**Model: IRM190, IRM190C (Celsius)**

Specialized thermometer with easy-to-read dual scale for meat and poultry. Glass lens makes it ovenproof. Large 1¾-inch dial. 5-inch stem. Temperature guide and pocket clip on ABS sheath. Field calibration.



Features	Target range indication
Certification	NSF <sup>®</sup> Certified
Antimicrobial Protection	BioCote <sup>®</sup>
Measurement Range	130 to 190°F/50 to 90°C
Unit of Measure	°F/°C
Accuracy	±2°F
Calibration	Boil test field calibration
Heat Resilience	Ovenproof
Water Resilience	Splash proof
Response Time	15 second response (approximate)
Housing Material	304 stainless steel
Display Material	Durable laboratory glass lens
Display Size	1.75"/4.4 cm dial
Probe Type	Bimetal
Probe Material	304 stainless steel
Probe Length	5"/12.7 cm stem
Probe Diameter	3 mm tip
Resolution	2°F/1°C
Casing	Sheath
Temperature Guide	USDA safe food temperature guide on thermometer
Mounting	Pocket clip
Dimensions	1.75 W x 5.5 H x 1.75 D (in)/4.4 W x 14.0 H x 4.4 D (cm)
Weight	1.0 oz / 28.3 g
Warranty	5-Year Limited Warranty