

## Cooking Thermometer

**Model: IRT220, IRT220-X2 (Twin Pack), IRT220-PACK (12 Pack)**

Our most popular bimetal model, also known as a chef's thermometer. Safe for commercial dishwashers and field calibration. Calibration tool and pocket clip on ABS sheath with BioCote<sup>®</sup>. Shatterproof lens. 1-inch magnified dial. Private label options available.



Features	1"/2.5 cm magnified dial
Certification	NSF <sup>®</sup> Certified
Antimicrobial Protection	BioCote <sup>®</sup>
Measurement Range	0 to 220°F
Unit of Measure	°F
Accuracy	±2°F
Calibration	Field calibration
Water Resilience	Safe for commercial dishwashers
Response Time	15 second response (approximate)
Housing Material	304 stainless steel
Display Material	Shatterproof lens
Display Size	1"/2.5 cm magnified dial
Probe Type	Bimetal
Probe Material	304 stainless steel
Probe Length	5"/12.7 cm stem
Probe Diameter	3 mm tip
Resolution	2°F
Casing	Sheath
Mounting	Pocket clip
Dimensions	1 W x 5.5 H x 1 D (in)/2.5 W x 14.0 H x 2.5 D (cm)
Weight	0.6 oz / 17 g
Warranty	5-Year Limited Warranty
Optional Accessories	AD-F