

Multi-Mount Oven Thermometer

Model: MOT1

Magnetic, hang, or stand mount. Monitors exact oven temperatures 100 to 600°F/50 to 300°C. 304 stainless steel housing and laboratory glass lens.



Features	Flexible mounting options
Measurement Range	100 to 600°F/50 to 300°C
Unit of Measure	°F/°C
Heat Resilience	Ovenproof
Housing Material	304 stainless steel housing
Display Material	Durable laboratory glass lens
Display Size	1.75"/4.4 cm dial
Resolution	25°F/10°C
Mounting	Magnetic, hang, or stand in oven
Dimensions	2.25 W x 2.75 H x 0.5 D (in)/5.7 W x 7.0 H x 1.3 D (cm)
Weight	1.8 oz / 51 g
Warranty	5-Year Limited Warranty