

## High Heat Oven Thermometer

### Model: POT750X

Monitors exact oven and holding temperatures 100 to 180°F/38 to 82°C. 304 stainless steel housing and laboratory glass lens. Stands or hangs in oven.



Features	Wide temperature range
Certification	NSF <sup>®</sup> Certified
Measurement Range	100 to 750°F/50 to 400°C
Unit of Measure	°F/°C
Heat Resilience	Ovenproof
Housing Material	304 stainless steel housing
Display Material	Durable laboratory glass lens
Display Size	2"/5.1 cm dial
Resolution	25°F/10°C
Mounting	Stand or hangs in oven
Dimensions	2.5 W x 3.75 H x 1.75 D (in)/6.4 W x 9.5 H x 4.4 D (cm)
Weight	1.4 oz / 39.7 g
Warranty	5-Year Limited Warranty