

Digital Scale

Models: SD1104-S (Silver), SD1104-BK (Black), SD1104-R (Red)

A member of the *Basic Scales* series, this scale features a traditional scale design upgraded with a stainless steel platform. Easy to use, with a backlit display and self-explanatory buttons. Available in silver, black or red.



Features	Selectable units, tare function, backlit display, overload indication, battery status indication, stainless steel platform, on/off button
Certification	WEEE, CE
Measurement Range	11 lb/176 oz/5 kg capacity
Unit of Measure	g/fl oz/lb:oz/ml
Tare	Tare function
Accuracy	0.4% ± 1 d
Response Time	1 second response
On/Off	On/off button
Auto-off	Auto-off after 30 seconds
Housing Material	ABS plastic
Display Material	LCD
Display Size	2.0 W x 1.0 H (in)/5.1 W x 2.5 H (cm)
Load Cell	Single point load cell
Platform Material	201 stainless steel
Platform Size	4.5"/14 cm diameter stainless steel platform
Resolution	1 g, 0.1 fl oz, 0 lb:0.1 oz, 1 ml
Mounting	Hang
Operating Range	32 to 104°F/0 to 40°C/≤90% RH
Battery	Three 1.5V AAA IEC LR03 (WERCSmart) alkaline batteries, included
Battery Life	10 months (3 times/day, 30 s/time)
Dimensions	6.0 W x 8.125 H x 1.0 D (in)/15.2 W x 20.6 H x 2.6 D (cm)
Weight	10.8 oz / 308 g (including battery)
Warranty	1-Year Limited Warranty