



TS-251D-2G

CPU	Intel® Celeron® J4025/J4005 dual-core 2.0 GHz processor
CPU Architecture	64-bit x86
Graphic Processors	Intel® HD Graphics 600
Floating Point Unit	Yes
Encryption Engine	Yes (AES-NI)
Hardware-accelerated Transcoding	Yes
System Memory	2 GB SO-DIMM DDR4 (1 x 2 GB)
Maximum Memory	8 GB (2 x 4GB)
Memory Slot	2 x SO-DIMM DDR4
Flash Memory	4GB (Dual boot OS protection)
Drive Bay	2 x 3.5-inch SATA 6Gb/s, 3Gb/s
Drive Compatibility	3.5-inch SATA hard disk drives 2.5-inch SATA hard disk drives 2.5-inch SATA solid state drives
Hot-swappable	Yes
M.2 SSD Slot	Optional via a QM2 PCIe adapter
SSD Cache Acceleration Support	Yes
Gigabit Ethernet Port (RJ45)	1
5 Gigabit Ethernet Port (5G/2.5G/1G/100M)	Expandable with an optional PCIe adapter
10 Gigabit Ethernet Port	Expandable with an optional PCIe adapter
Jumbo Frame	Yes
PCIe Slot	1 Slot 1: PCIe Gen 2 x4

USB 2.0 port	3
USB 3.2 Gen 1 port	2
USB 3.2 Gen 2 (10Gbps) Port	Optional via a PCIe expansion card
IR Sensor	Yes (Optional QNAP RM-IR004 remote control)
HDMI Output	1, HDMI 2.0
Form Factor	Tower
LED Indicators	Power/Status, LAN, USB, HDD1-2
Buttons	Power, USB copy, Reset
Dimensions (HxWxD)	168 × 105 × 226 mm
Weight (Net)	1.48 kg
Weight (Gross)	2.58 kg
Operating temperature	0 - 40 °C (32°F - 104°F)
Relative Humidity	5-95% RH non-condensing, wet bulb: 27°C (80.6°F)
Power Supply Unit	External Power Adapter, 65W, 100-240V
Power Consumption: HDD Sleep Mode	8.08 W
Power Consumption: Operating Mode, Typical	15.25 W
Fan	1 x 70mm
Sound Level	16.7 db(A)
System Warning	Buzzer
Kensington Security Slot	Yes
Max. Number of Concurrent Connections (CIFS)	800

Note: Use only QNAP memory modules to maintain system performance and stability. For NAS devices with more than one memory slot, use QNAP modules with identical specifications. Warning: Using unsupported modules may degrade performance, cause errors, or prevent the operating system from starting.

* Sound Level Test Environment: Refer to ISO 7779; Maximum HDD loaded; Bystander Position; Average data from 1 meter in front of operating NAS.

Designs and specifications are subject to change without notice.